













Ordering Information

283 is the basic model number. The chart below illustrates the combinations that are available. To order, fill in the necessary numbers needed to indicate the complete part number. All 283 Series masks include 5' tubing.



Mask	Description	Mask Type	No.
14028	K.S. disposable mask	K.S. disposable	01
800623-00	Duo-Seal® mask	Duo-Seal mask	12
800623-01	Duo-Seal® mask with 802754-04 microphone/switch assembly and plug assembly (PJ-068 Type)	Duo-Seal mask	13
800717-00	Sky Mask	Sky mask	14
800717-01	Sky Mask with 800777-00 carbon microphone. Switch and plug assembly (PJ-068 Type)	Sky mask	15
800623-02	Duo-Seal® mask with 802754-05 microphone and plug assembly (PJ-068 Type)	Duo-Seal mask	16
800717-02	Sky Mask with 800777-00 carbon microphone and plug assembly (PJ-068 Type)	Sky mask	17
802928-01	Duo-Seal® mask with one piece head harness and 802606-01 dynamic microphone	Duo-Seal mask	18
802928-02	Duo-Seal® mask with one piece head harness	Duo-Seal mask	19
20776-01	249 constant flow mask	249 mask	20
20776-01	249 constant flow mask with dynamic microphone, pre-amp, and PJ-068 plug	249 mask	21
20776-01	249 constant flow mask with 802754-05 carbon microphone and PJ-068 plug	249 mask	22
800623-04	Duo-Seal® mask with 803557-02 electret microphone and plug assembly (PJ-068 Type)	Duo-Seal mask	23
802928-03	Duo-Seal® mask with one piece head harness, 803557-02 electret microphone, and plug assembly (PJ-068 Type)	Duo-Seal mask	24
802928-04	Duo-Seal® mask with one piece head harness and 803602-01 dynamic microphone assembly	Duo-Seal mask	25
14025-00	K.S. disposable "kiddie" (child's) mask	K.S. disposable	26

Flow Indicator	No.
Without flow indicator	0
8540-00 	1

Connector	Description	No.
Without Connector		0
8570-00 ¹ No Stripe	Avox (2.5 lpm) 	1
5065-10	AN type 	2
29559	ARO type 	3
14807	Puritan type 	4
8570-03 ¹ Red Stripe	Avox (2.0 lpm) (similar to 8570-00) 	6
8570-01 ¹ Gold Stripe	Avox (1.5 lpm) (similar to 8570-00) 	7
8586	Avox Therapeutic (7.5 lpm) 	8
8570-05 ¹ Green Stripe	Avox (3.0 lpm) (similar to 8570-00) 	9
802039-01	Cessna 	A
289-57	ARO type (90°) 	B

Note: For mating outlets see catalog sheet AVIA 5250.

¹ Oxygen pressure in line must be 55 PSIG at 20,000 ft. to produce lpm values in all 8570 series connectors

WARNING: IMPROPER USE OR IMPROPER MAINTENANCE OF THIS EQUIPMENT MAY RESULT IN SERIOUS PERSONAL INJURY OR DEATH. THESE ASSEMBLIES ARE INTENDED TO BE USED ONLY FOR AVIATION APPLICATIONS AS COMPONENTS OF A COMPLETE AVIATION OXYGEN SYSTEM USED ONLY BY, OR UNDER THE SUPERVISION OF, A PILOT OR CREW MEMBER TRAINED AND QUALIFIED IN ITS USE. THIS EQUIPMENT IS TO BE SERVICED ONLY BY SERVICE TECHNICIANS TRAINED IN THE INHERENT HAZARDS OF HIGH PRESSURE AVIATION OXYGEN AND KNOWLEDGEABLE IN THIS EQUIPMENT. THE NAMES OF AUTHORIZED SERVICE CENTERS ARE AVAILABLE FROM AVOX SYSTEMS OR YOUR AUTHORIZED AVOX DISTRIBUTOR. THIS EQUIPMENT IS TO BE USED ONLY WITH AVIATION BREATHING OXYGEN PER MIL-PRF-27210.